


[Home Page](#)
[Company Information](#)
[Products](#)
[Contact Us](#)
[What's New](#)
[How to Choose](#)
[Product Specifications](#)
[Product Features](#)
[STC Home](#)


BELCO Sealer Tunnel Combinations

Product Specifications

STC 2016 -Economy

This manually operated shrink packaging system features a full sized 20" Long x 16" Wide seal area and has a tunnel opening 18" Wide x 8" High. Rated for packaging speeds of 5-7 products per minute, this machine is built to provide years of trouble free production.

STC 2016 -Standard

Available with all the popular options, this machine has a seal area of 20" Long x 16" Wide. The STC 2016 shrink tunnel is 18" Wide x 8" High and has a Watlow digital temperature control, top and bottom fan controls and variable speed conveyor. Semi-automatic operation can produce 15-18 packages per minute. The machine is built to perform in multiple shift facilities.

STC 2520

One of Belco's most popular models, the STC 2520 has a sealing size of 25" Long x 19" Wide and features the Lighted Viewing Window as a standard included option to help make product change-overs and tunnel set-ups fast and easy. The shrink tunnel chamber size of 21" Wide x 8" High x 36" Long, Watlow digital temperature control, top and two bottom fan controls and variable speed conveyor allow for semi-automatic operation ranging from 18-25 packages per minute. Multiple shift operation and years of trouble free production can be expected from this machine.



STC Combination Machines

Model Number	Conveyor Style	Conveyor Height (Inches)	Max Conveyor Speed (ft/min)		Tunnel Dimensions (Inches)			Temp Control	Seal Area		Optional Air Requirements		Maximum Film Roll	Space Requirements (Inches)			Power Requirements			Ship Weight (lbs)
			Belt	Rod	Wide	Long	High		Long	Wide	CF/C	PSI		Wide	Long	High	Volts	Amps	Phase	
STC"ECO"	Belt	33-36	60	N/A	18	24	8	F	20"	16"	N/A	N/A	26"	34	92	58	240	35	1	550
STC2016	Belt/Rod	33-36	60	90	18	24	8	F/C	20"	16"	.02	80	26"	34	92	58	240	35	1	625
STC2520	Belt/Rod	33-36	60	90	21	36	8	F/C	25"	19"	.02	80	29"	37	124	58	240	45	1	950

For STC's equipped with the optional powered film unwind add 14" to the overall width of the machine and subtract 4" from the overall length.

** CF/C: cubic feet / cycle

* The film roll cradle may not accept the same size centerfold film.
Check maximum film size for your application.

[Home](#) | [Company Information](#) | [Products](#) | [Contact Us](#) | [What's New](#)

[Manual Sealers](#) | [Automatic Sealers](#) | [Medical Sealers](#) |
[Blister Sealers](#) | [Accessories](#) | [Minipack-Torre](#)

Belco Packaging Systems, Inc.

800-833-1833

626-357-9566 * FAX: 626-359-3440

Email : info@belcopackaging.com